



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Lace Closing, Tin-Coated Bronze, 0.63-0.74"

By Bryant
Catalog # [SPS062SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Lace Closing, Tin- Coated Bronze, 0.63-0.74"



Features

- Offset Eye
- Split Mesh
- Lace Closing
- Tin- Coated Bronze
- 0.63-0.74"

Application

Offset Eye

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 0.63 in-0.74 in
Cable Size .63-.74" (1.60-1.88)

Force Related

Approx Breaking Strength 750 lb.

General

Construction Woven
Material - Mounting Hardware Screw Hook or Beam Clamp
Type Offset Eye
Series Standard Duty Series
OEM Brand Name Hubbell Bryant
Material Bronze, Tin Coated
UPC 781786372443
Style Split Mesh, Lace Closing

Logistics

Carton Quantity 50

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)