



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Lace Closing, Tin-Coated Bronze, 1.00-1.24"

By Bryant
Catalog # [SPS100SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Lace Closing, Tin- Coated Bronze, 1.00-1.24"



Features

- Offset Eye
- Split Mesh
- Lace Closing
- Tin- Coated Bronze
- 1.00-1.24"

Application

Offset Eye

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 1-1.24 in
Cable Size 1.00-1.24" (2.54-3.15)

Force Related

Approx Breaking Strength	1,500 lb.
General	
Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Offset Eye
Series	Standard Duty Series
OEM Brand Name	Hubbell Bryant
Material	Bronze, Tin Coated
UPC	781786372481
Style	Split Mesh, Lace Closing

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)