



Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Lace Closing, Tin-Coated Bronze, 1.25-1.49"

By Bryant
Catalog # [SPS125U](#)

Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Lace Closing, Tin-Coated Bronze, 1.25-1.49"

Features

- Single Eye
- Split Mesh
- Lace Closing
- Tin-Coated Bronze
- 1.25-1.49"

Application

Single Eye

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.25 in-1.49 in
Cable Size 1.25-1.49" (3.17-3.78)

Force Related



Approx Breaking Strength 1,610 lb.

General

Construction Woven
Material - Mounting Hardware Screw Hook or Beam Clamp
Type Single Eye
Series Standard Duty Series
OEM Brand Name Hubbell Bryant
Material Bronze, Tin Coated
UPC 781786245761
Style Split Mesh, Lace Closing

Logistics

Carton Quantity 5

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)