



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Lace Closing, Tin-Coated Bronze, 3.00-3.49"

By Bryant

Catalog # [SPS300SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Lace Closing, Tin-Coated Bronze, 3.00-3.49"



Features

- Offset Eye
- Split Mesh
- Lace Closing
- Tin-Coated Bronze
- 3.00-3.49"

Application

Offset Eye

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 3 in-3.49 in
 Cable Size 3.00-3.49" (7.62-8.86)

Force Related

Approx Breaking Strength 3,250 lb.

General

Construction Woven
 Material - Mounting Hardware Screw Hook or Beam Clamp
 Type Offset Eye
 Series Standard Duty Series
 OEM Brand Name Hubbell Bryant
 Material Bronze, Tin Coated
 UPC 781786372214
 Style Split Mesh, Lace Closing

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)