



# Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.63-0.74"

By Bryant  
Catalog # [SPSR062SO](#)



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.63-0.74"

## Features

- Offset Eye
- Split Mesh
- Rod Closing
- Tin-Coated Bronze
- 0.63-0.74"

## Application

Offset Eye

## General

Approx Breaking Strength	750 lbs
Catalog Number	SPSR062SO
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated

Material - Mounting Hardware Series	Screw Hook or Beam Clamp Standard Duty
Style	Split Mesh, Rod Closing
Type	Offset Eye
UPC	781786371934

## Conductor Related

Cable Diameter Range	0.63 in-0.74 in
Cable Size	.63-.74" (1.60-1.88)

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - SPSR062SO Specification Sheet French](#)
- [Specifications - SPSR062SO Specification Sheet English](#)