



Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.63-0.74"

By Bryant
Catalog # [SPSR062U](#)

Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.63-0.74"



Features

- Single Eye
- Split Mesh
- Rod Closing
- Tin-Coated Bronze
- 0.63-0.74"

Application

Single Eye

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.63 in-0.74 in
Cable Size .63-.74" (1.60-1.88)

Force Related

Approx Breaking Strength 790 lb.

General

| | |
|------------------------------|--------------------------|
| Construction | Woven |
| Material - Mounting Hardware | Screw Hook or Beam Clamp |
| Type | Single Eye |
| Series | Standard Duty Series |
| OEM Brand Name | Hubbell Bryant |
| Material | Bronze, Tin Coated |
| UPC | 781786246386 |
| Style | Split Mesh, Rod Closing |

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)