



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 1.00-1.24"

By Bryant
Catalog # [SPSR100SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 1.00-1.24"

Features

- Offset Eye
- Split Mesh
- Rod Closing
- Tin-Coated Bronze
- 1.00-1.24"

Application

Offset Eye

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 1-1.24 in
Cable Size 1.00-1.24" (2.54-3.15)

Force Related



Approx Breaking Strength 1,500 lb.

General

Construction Woven
Material - Mounting Hardware Screw Hook or Beam Clamp
Type Offset Eye
Series Standard Duty Series
OEM Brand Name Hubbell Bryant
Material Bronze, Tin Coated
UPC 781786372221
Style Split Mesh, Rod Closing

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)