



## Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Stainless Steel, 1.00-1.24"

By Bryant  
Catalog # [SPSR100SOS](#)

Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Stainless Steel, 1.00-1.24"



### Features

- Offset Eye
- Split Mesh
- Rod Closing
- Stainless Steel
- 1.00-1.24"

### Application

Offset Eye

### Specifications

EU RoHS Indicator No

### Conductor

Cable Diameter Range 1-1.24 in  
Cable Size 1.00-1.24" (2.54-3.15)

### Force Related

Approx Breaking Strength 2,500 lb.

### General

Construction Woven  
Material - Mounting Hardware Screw Hook or Beam Clamp  
Type Offset Eye  
Series Standard Duty Series  
OEM Brand Name Hubbell Bryant  
Material Stainless Steel  
UPC 781786372146  
Style Split Mesh, Rod Closing

### Logistics

Carton Quantity 5

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)