



Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Rod Closing, Stainless Steel, 1.00-1.24"

By Bryant
Catalog # [SPSR100US](#)



Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Rod Closing, Stainless Steel, 1.00-1.24"

Features

- Single Eye
- Split Mesh
- Rod Closing
- Stainless Steel
- 1.00-1.24"

Application

Single Eye

General

Approx Breaking Strength	2,650 lbs
Catalog Number	SPSR100US
Construction	Woven
EU RoHS Indicator	No
Material	Stainless Steel

Material - Mounting Hardware Series	Screw Hook or Beam Clamp Standard Duty
Style	Split Mesh, Rod Closing
Type	Single Eye
UPC	781786371989

Conductor Related

Cable Diameter Range	1-1.24 in
Cable Size	1.00-1.24" (2.54-3.15)

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - SPSR100US Specification Sheet English](#)
- [Specifications - SPSR100US Specification Sheet French](#)