



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 1.25-1.49"

By Bryant
Catalog # [SPSR125SO](#)



Wire and Cable Management, Support Grip, Offset Eye, Split
Mesh, Rod Closing, Tin-Coated Bronze, 1.25-1.49"

Features

- Offset Eye
- Split Mesh
- Rod Closing
- Tin-Coated Bronze
- 1.25-1.49"

Application

Offset Eye

General

Approx Breaking Strength	1,500 lbs
Catalog Number	SPSR125SO
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated

Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Style	Split Mesh, Rod Closing
Type	Offset Eye
UPC	781786372245

Conductor Related

Cable Diameter Range	1-1.24 in
Cable Size	1.25-1.49" (3.17-3.78)

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - SPSR125SO Specification Sheet French](#)
- [Specifications - SPSR125SO Specification Sheet English](#)