



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Stainless Steel, 1.25-1.49"

By Bryant
Catalog # [SPSR125SOS](#)

Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Stainless Steel, 1.25-1.49"



Features

- Offset Eye
- Split Mesh
- Rod Closing
- Stainless Steel
- 1.25-1.49"

Application

Offset Eye

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 1.25 in-1.49 in
Cable Size 1.25-1.49" (3.17-3.78)

Force Related

Approx Breaking Strength 4,200 lb.

General

Construction Woven
Material - Mounting Hardware Screw Hook or Beam Clamp
Type Offset Eye
Series Standard Duty Series
OEM Brand Name Hubbell Bryant
Material Stainless Steel
UPC 781786372160
Style Split Mesh, Rod Closing

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)