



# Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 1.25-1.49"

By Bryant  
Catalog # SPSR125U



Wire and Cable Management, Support Grip, Single Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 1.25-1.49"

## Features

- Single Eye
- Split Mesh
- Rod Closing
- Tin-Coated Bronze
- 1.25-1.49"

## Application

Single Eye

## General

Approx Breaking Strength	1,610 lbs
Catalog Number	SPSR125U
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated

Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Style	Split Mesh, Rod Closing
Type	Single Eye
UPC	781786246447

## Conductor Related

Cable Diameter Range	1.25 in-1.49 in
Cable Size	1.25-1.49" (3.17-3.78)

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - SPSR125U Specification Sheet French](#)
- [Specifications - SPSR125U Specification Sheet English](#)