



Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 3.00-3.49"

By Bryant
Catalog # [SPSR300SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Split Mesh, Rod Closing, Tin-Coated Bronze, 3.00-3.49"

Features

- Offset Eye
- Split Mesh
- Rod Closing
- Tin-Coated Bronze
- 3.00-3.49"

Application

Offset Eye

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 2.5 in-2.99 in
Cable Size 3.00-3.49" (7.62-8.86)

Force Related



Approx Breaking Strength	4,300 lb.
General	
Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Offset Eye
Series	Standard Duty Series
OEM Brand Name	Hubbell Bryant
Material	Bronze, Tin Coated
UPC	781786372092
Style	Split Mesh, Rod Closing

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)