



Bryant, Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .50-.61" Cable Range

By Bryant
Catalog # [SSR050](#)

Bryant, Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .50-.61" Cable Range

Features

- Split Mesh
- Rod Closing
- Offset Eye
- .50-.61" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range	0.50 in-0.61 in
Cable Specification	UL Listed Circuit Wire
Cable Size	.50-.61" (1.27-1.55)

Force Related

Approx Breaking Strength	1,500 lb.
Load Capacity	300

General

Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Offset Eye
Series	Slack Grip
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786271685
Style	Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)