



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .62-.74" Cable Range

By Bryant
Catalog # [SSR062](#)

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .62-.74" Cable Range



Features

- Split Mesh
- Rod Closing
- Offset Eye
- .62-.74" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.62 in-0.74 in
Cable Specification UL Listed Circuit Wire
Cable Size .62-.74" (1.57-1.88)

Force Related

Approx Breaking Strength 1,800 lb.
Load Capacity 360

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Offset Eye
Series Slack Grip
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786271708
Style Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)