



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .75-.99" Cable Range

By Bryant
Catalog # [SSR075](#)

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, .75-.99" Cable Range



Features

- Split Mesh
- Rod Closing
- Offset Eye
- .75-.99" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.75 in-0.99 in
Cable Specification UL Listed Circuit Wire
Cable Size .75-.99" (1.90-2.51)

Force Related

Approx Breaking Strength 2,200 lb.

Load Capacity 440

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Offset Eye
Series Slack Grip
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786271722
Style Split Mesh, Rod Closing, Single Weave

Logistics

Carton Quantity 2

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)