



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.00-1.24" Cable Range

By Bryant
Catalog # SSR100



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.00-1.24" Cable Range

Features

- Split Mesh
- Rod Closing
- Offset Eye
- 1.00-1.24" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.00-1.24 in
Cable Specification UL Listed Circuit Wire
Cable Size 1.00-1.24" (2.54-3.15)

Force Related

Approx Breaking Strength 3,400 lb.
Load Capacity 680

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Offset Eye
Series Slack Grip
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786271746
Style Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)