



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.25-1.49" Cable Range

By Bryant
Catalog # SSR125

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.25-1.49" Cable Range



Features

- Split Mesh
- Rod Closing
- Offset Eye
- 1.25-1.49" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.25 in-1.49 in
Cable Specification UL Listed Circuit Wire
Cable Size 1.25-1.49" (3.17-3.78)

Force Related

Approx Breaking Strength 4,500 lb.
Load Capacity 900

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Offset Eye
Series Slack Grip
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786271760
Style Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)