



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.50-1.74 inch Cable Range

By Bryant
Catalog # SSR150

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 1.50-1.74 inch Cable Range

Features

- Split Mesh
- Rod Closing
- Offset Eye
- 1.50-1.74 inch Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range	1.50 in-1.74 in
Cable Specification	UL Listed Circuit Wire
Cable Size	1.50-1.74 inch (3.81-4.42)

Force Related

Approx Breaking Strength	5,800 lb.
Load Capacity	1160

General

Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Offset Eye
Series	Slack Grip
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786271784
Style	Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)