



Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.50-2.99 inch Cable Range

By Bryant
Catalog # [SSR250](#)

Bryant Wire and Cable Management, Pulling Grip, Split Mesh, Rod Closing, Offset Eye, 2.50-2.99 inch Cable Range

Features

- Split Mesh
- Rod Closing
- Offset Eye
- 2.50-2.99 inch Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range	2.50 in-2.99 in
Cable Specification	UL Listed Circuit Wire
Cable Size	2.50-2.99 inch (6.35-7.59)

Force Related

Approx Breaking Strength	11,000 lb.
Load Capacity	2200

General

Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Offset Eye
Series	Slack Grip
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786271845
Style	Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)