



Bryant Wire and Cable Management,
Pulling Grip, Split Mesh, Rod Closing, Offset
Eye, 3.50-3.99" Cable Range

By Bryant
Catalog # [SSR350](#)

Bryant Wire and Cable Management, Pulling Grip, Split Mesh,
Rod Closing, Offset Eye, 3.50-3.99" Cable Range



Features

- Split Mesh
- Rod Closing
- Offset Eye
- 3.50-3.99" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 3.50 in-3.99 in
Cable Specification UL Listed Circuit Wire
Cable Size 3.50-3.99" (8.89-10.13)

Force Related

Approx Breaking Strength 12,000 lb.

Load Capacity 2400

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Offset Eye
Series Slack Grip
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786271883
Style Split Mesh, Rod Closing, Single Weave

Logistics

Carton Quantity 2

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)