



Temporary Power Products, Distribution Boxes, Complete Unit, Locking Style, 50A 125/250V, Yellow

By Bryant
Catalog # [TPDLB](#)

Temporary Power Products, Distribution Boxes, Complete Unit, Locking Style, 50A 125/250V, Yellow



Features

- Complete Unit
- Locking Style
- 50A 125/250V
- Yellow

Application

Portable/Temporary

Specifications

| | |
|--------------------------|--------------------|
| Environmental Conditions | Indoor and Outdoor |
| EU RoHS Indicator | No |
| Nema Rating | Muli Outlet |

Conductor

| | |
|-----------------|------------------|
| Number Of Wires | 4-Wire Grounding |
| Wire Size | Pre-Wired |
| Number Of Poles | 3-Pole |

Current

| | |
|---------------------------|--------------|
| Phase | Single Phase |
| Current / Amperage Rating | 50 A |

| | |
|----------------|-------------|
| Connectivity | Plug-In |
| Current Rating | 50 A |
| Wattage | 12500 |
| Voltage Rating | 120/240 VAC |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

General

| | |
|------------------------------|---------------------------|
| Item Type | Unit with Locking Devices |
| Material - Mounting Hardware | Free Standing |
| Type | Twist-Lock® |
| Series | Distribution Box |
| OEM Brand Name | Hubbell Bryant |
| Material | Composite |
| UPC | 781786141469 |
| Color | Yellow |

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)