



Temporary Power Products, Distribution Boxes, Complete Unit, Straight Blade Style, 50A 125/250V, Yellow

By Bryant
Catalog # TPDSB



Temporary Power Products, Distribution Boxes, Complete Unit, Straight Blade Style, 50A 125/250V, Yellow

Features

- Complete Unit
- Straight Blade Style
- 50A 125/250V
- Yellow

Application

Portable/Temporary

Specifications

Environmental Conditions	Indoor and Outdoor
EU RoHS Indicator	No
Nema Rating	Muli Outlet

Conductor

Number Of Wires	4-Wire Grounding
Wire Size	Pre-Wired
Number Of Poles	3-Pole

Current

Phase	Single Phase
Current / Amperage Rating	50 A

Connectivity	Plug-In
Current Rating	50 A
Wattage	12500
Voltage Rating	120/240 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Item Type	Unit with Straight Blade Devices
Material - Mounting Hardware Type	Free Standing Straight Blade Distribution Box
Series	Hubbell Bryant
OEM Brand Name	Hubbell Bryant
Material	Composite
UPC	781786141452
Color	Yellow

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)