



15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Ivory

By Bryant
Catalog # [USBB15C5IWR](#)

15A/125V Tamper Resistant/Weather Resistant Duplex Receptacle & Type C USB Port, Ivory



Features

- Ivory

Specifications

Nema Rating 5-15R

Conductor

Number Of Poles 2
Number Of Wires 3

Current

Current / Amperage Rating 15 A
Voltage Rating Description 125 V

General

Type Two Type-C USB Ports
Series USB Charger
Style Style Line Decorator
Color Ivory