



NEMA 12 Filter Fan 115 Volt 9 Cubic Feet Per Minute 4.2X4.2 -Light Gray

By Wiegmann
Catalog # [FF449CFM115VG](#)

NEMA 12 Filter Fan 115 Volt 9 Cubic Feet Per Minute 4.2X4.2 -
Light Gray

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

Ventilation;Temperature Control

Specifications

Certified Listed	UL/cUL Recognized
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	No
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Actual Height	4.2 in
---------------	--------



Actual Depth	2.6 in
Actual Width	4.2 in
Depth	3 in
Width	4 in
Height	4 in

General

Type	Filter Fan
Material	ABS Plastic
UPC	786725886357
Color	Gray

Logistics

Carton Quantity	16
-----------------	----

Product Assets

[Catalog \[English\]](#)