

## Extra Heavy Duty Industrial Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, Brown

By Hubbell Wiring Device-Kellems  
Catalog # [GFSG5262](#)



Industrial Grade TRWR Ground Fault Receptacle 15A

### Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

### Application

Industrial Grade

### Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

### Conductor

Wire Size	#14 - #10 AWG
-----------	---------------

### Current

Phase	Single Phase
Current / Amperage Rating	15 A
Wattage	1875 W
Voltage Rating	125 VAC

### Dimensions

Size	4.06 in x 1.75 in x 1.48 in
------	-----------------------------

Width	1.75 in
Height	4.06 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.06 in

### General

Item Type	Style Line GFCI Receptacle Tamper-Resistant/Weather-Resistant
Type	
Series	Extra Heavy Duty
Material	PC/PBT
Specifications	<ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - PC/PBT</li><li>• Ground Contacts - Nickel Plated Brass</li><li>• Mounting Screws - Stainless Steel</li><li>• Mounting Strap -Nickel Plated Brass</li></ul>
UPC	783585745886
Color	Brown

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)