

HUBBELL Premise Wiring

PLUGTRAK TAMPER RESIST 15A 5FT ALUM



By Hubbell Premise Wiring
Catalog # [HBLALU20GB512TR](#)

PLUGTRAK TAMPER RESIST 15A 5FT ALUM

Features

- Multiple spacing configurations
- Satin anodized scratch resistant finish
- Hubbell designed and manufactured single receptacle
- Insulation displacement wiring provides superior wire retention

Performance

Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R,
Mechanical - Wire - #12 AWG Stranded Copper

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E253976 /E253830 /E253833• UL Standard UL 5
EU RoHS Indicator	Contact Manufacturer

Conductor

Wire Size	#12 AWG THHN
-----------	--------------

Configuration

Number Of Receptacles	5
-----------------------	---

Current

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

Dimensions

Length	5 ft
--------	------

General

Item Type	Aluminum Pre-Wired PlugTrak
Type	Single Circuit
Series	Aluminum
Specifications	<ul style="list-style-type: none">• Circuits - TR/Single• Material - Anodized Aluminum• Number of Receptacles - 5 Singles• PlugTrak Length - 5 Foot• Receptacle Face - Thermoplastic• Receptacle Spacing - 12 Inch
UPC	783585455945
Style	Tamper Resistant

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)