

HUBBELL Premise Wiring

PLUGTRAK, 15A, 2 CIRC,12 RCPT, 6',ALU

By Hubbell Premise Wiring
Catalog # [HBLALU20GBA606](#)

PLUGTRAK, 15A, 2 CIRC,12 RCPT, 6',ALU

Features

- Multiple spacing configurations
- Satin anodized scratch resistant finish
- Hubbell designed and manufactured single receptacle
- Insulation displacement wiring provides superior wire retention

Performance

Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R,
Mechanical - Wire - #12 AWG Stranded Copper

Specifications

| | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E253976 /E253830 /E253833• UL Standard UL 5 |
| EU RoHS Indicator | Contact Manufacturer |

Conductor

| | |
|-----------|--------------|
| Wire Size | #12 AWG THHN |
|-----------|--------------|

Configuration

| | |
|-----------------------|----|
| Number Of Receptacles | 12 |
|-----------------------|----|

Current

| | |
|---------------------------|---------|
| Current / Amperage Rating | 15 A |
| Voltage Rating | 125 VAC |

Dimensions

| | |
|--------|------|
| Length | 6 ft |
|--------|------|

General

| | |
|----------------|---|
| Item Type | Aluminum Pre-Wired PlugTrak |
| Type | Two Circuits |
| Series | Aluminum |
| Specifications | <ul style="list-style-type: none">• Circuits - Two• Material - Anodized Aluminum• Number of Receptacles - 12 Singles• PlugTrak Length - 6 Foot• Receptacle Face - Thermoplastic• Receptacle Spacing - 6 Inch |
| UPC | 783585113296 |
| Style | Standard |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 2 |
|-----------------|---|

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)