

# HUBBELL Premise Wiring

## Metal Raceway, PlugTrak, Isolated Ground, 20A 125V, 1 Circuit, 12 Receptacle, 6' Aluminum

By Hubbell Premise Wiring  
Catalog # [HBLALU20IG606](#)

Metal Raceway, PlugTrak, Isolated Ground, 20A 125V, 1 Circuit, 12 Receptacle, 6' Aluminum

### Features

- Multiple spacing configurations
- Satin anodized scratch resistant finish
- Hubbell designed and manufactured single receptacle
- Insulation displacement wiring provides superior wire retention

### Performance

Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R,  
Mechanical - Wire - #12 AWG Stranded Copper

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 no. 62</li><li>• E253976 /E253830 /E253833</li><li>• UL Standard UL 5</li></ul>
EU RoHS Indicator	Contact Manufacturer

### Conductor

Wire Size	#12 AWG THHN
-----------	--------------

### Configuration

Number Of Receptacles	12
-----------------------	----

### Current

Current / Amperage Rating	15 A
Voltage Rating	125 VAC



### Dimensions

Length	6 ft
--------	------

### General

Item Type	Aluminum Pre-Wired PlugTrak
Type	Single Circuit
Series	Aluminum
Specifications	<ul style="list-style-type: none"><li>• Circuits - IG/Single</li><li>• Material - Anodized Aluminum</li><li>• Number of Receptacles - 12 Singles</li><li>• PlugTrak Length - 6 Foot</li><li>• Receptacle Face - Thermoplastic</li><li>• Receptacle Spacing - 6 Inch</li></ul>
UPC	783585113326
Style	Isolated Ground

### Logistics

Carton Quantity	2
-----------------	---

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)