

PlugTrak, Aluminum, Tamper Resistant,
20A Circuit, 5 Receptacle, 5' Aluminum



By Hubbell Premise Wiring
Catalog # [HBLALU24GB512](#)

PlugTrak, Aluminum, Tamper Resistant, 20A Circuit, 5 Receptacle,
5' Aluminum

Features

- Multiple spacing configurations
- Satin anodized scratch resistant finish
- Hubbell designed and manufactured single receptacle
- Insulation displacement wiring provides superior wire retention

Performance

Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R,
Mechanical - Wire - #12 AWG Stranded Copper

Specifications

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E253976 /E253830 /E253833 • UL Standard UL 5
EU RoHS Indicator	Contact Manufacturer

Conductor

Wire Size	#12 AWG THHN
-----------	--------------

Configuration

Number Of Receptacles	5
-----------------------	---

Current

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

Dimensions

Length	5 ft
--------	------

General

Item Type	Aluminum Pre-Wired PlugTrak
Type	Single Circuit
Series	Aluminum
Specifications	• Circuits - Single • Material - Anodized Aluminum • Number of Receptacles - 5 Singles • PlugTrak Length - 5 Foot • Receptacle Face - Thermoplastic • Receptacle Spacing - 12 Inch
UPC	783585113364
Style	Standard

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)