

Wire Management Products

Cord and Cable Reels

Industrial Power Cord Reels



Features

- Durable, Corrosion Resistant Cast Aluminum Construction
- Hospital Grade Devices
- Multi-Position Guide Arm can be mounted in two different positions
- UL Type 1

Ordering Information

Description	UPC	Catalog Number
White Industrial Reel with HBL8319C Hospital Grade Connector, UL Type 1, 45 Ft, #12/3 SJO, 20 A, 125 VAC	78358570863	HBLIWC45123C20HG

Listings

cULus Listed

Specifications

Spool	Aluminum
Guide Frame	Thermoplastic
Cord	Copper
Internal Terminals	Copper Alloy
Ball Stopper	Thermoplastic
Fitting	Aluminum

Performance

Electrical	
Amperage	20 A
Max. Working Voltage	125V AC

Moisture Resistance

Dry, Indoor, Non-Hazardous Locations - UL Type 1

Number of Wires

3-Wire	Environmental
--------	---------------



Online Resources

eCatalog

