



NEMA 4X Continuous Hinge Twist Latch With Window 30X20X10 Fiberglass-Opaque

By Wiegmann
Catalog # [HW-N4X302010CHW](#)

NEMA 4X Continuous Hinge Twist Latch With Window
30X20X10 Fiberglass-Opaque



*Representative Image

Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure
UPC	786725881291

Dimensions

Actual Depth	11.89 in
Actual Height	32.86 in
Actual Width	20.99 in
Cubic Capacity	6000 cu.in
Depth	10 in
Height	30 in
Weight	31.5 lb
Width	20 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Product Assets

[Catalogs - Wiegmann Non-Metallic Enclosures](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand