

Multi-Hole Cord Grip Connector

By Hubbell Wiring Device-Kellems
Catalog # [MHC1032CR](#)

(4) Holes 0.23-0.29" (5.8-7.4mm), 3/4" NPT, Gray Nylon



Features

- Nylon cord connector resists most common industrial corrosives
- Ergonomic design makes them easy to handle and maintain UL listing by hand tightening
- Internal bushing accomodates up to four individual conductors

Application

Terminating Portable Cords into an Enclosure

Performance

Withstands 100lbs of pullout force

Specifications

Industry Standard(s)	UL Listed
Environmental Conditions	Hazardous Locations - Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC

Conductor

Conductor Range	0.23-0.29" (5.8-7.4mm)
Number Of Conductors	Up to 4

Dimensions

Hub Size	3/4" NPT
----------	----------

General

Type	Straight Male
Series	Multi-Hole Cord Grip
UPC	783585708522
Style	Cord Connector
Color	Gray

Logistics

Carton Quantity	25
-----------------	----

Operational

Temperature Rating	-30°F to +225°F (-34°C to +107°C)
--------------------	-----------------------------------

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)