


Rack Mount Kit

Features

- Provides a Cost-Effective, Front Terminated, High-Density Rack Mount 100 Solution
- Cable Access Openings in Wiring Blocks Allow Cables to be Routed Through the Block Directly to the Point of Termination
- Unique Third Hand Locating Pins Hold Panel in Place on Rack While Installing Screws
- Rolled Edge Construction Provides Superior Strength During Termination



Ordering Information

Description	Catalog Number	UPC
NEXTSPEED Rack Mount Kit without Cable Management, 200-Pair, 2U Rack Unit, 5-Pair	110RM25NT	662620838632

Accessories

Hubbell Labeling Solution	XPL11010B
---------------------------	-----------

Listings

Verified to meet and exceed Category 5E ANSI/TIA/EIA-568-C.2 connecting hardware specifications

Online Resources

eCatalog

Specifications

Panel Material	14 ga. steel
Finish	Durable black powder coat
Organization	Optional rear cable organizer (HC36WF) clips to rear of panel
NEXT Performance	Increased Pair Isolation on 6-110 wiring and connecting blocks provided for superior NEXT performance
Flammability	110 wiring bases and blocks are made of fire-retardant plastic rated UL 94v-0

Performance

Electrical

Mounts directly to 19" EIA-310-D standard rack and cabinet

Applications

Compatible with Hubbell Labeling Software and laser-printable 110 paper label sheets