

HUBBELL Premise Wiring

6110PCL3

By Hubbell Premise Wiring
Catalog # [6110PCL3](#)



Patch Cord, 6-110 Factory Terminated Patch Cords, Cat6 (6-110 to 6-110), 3' Length

Features

- Plug Housing Includes Built-In Polarization to Ensure Proper Mating Connection to Connecting Blocks
- Angled Conductor Towers Separate Paired Conductors and makes Pair Splitting and Conductor Lacing Simple
- Cable Ties Secure Cable to Cover for Easy Termination and Strain Relief

Performance

Electrical - Terminates 24 to 26 AWG solid or 7-strand twisted-pair cable -

General

Attenuation	.1dB
Boot Type	Polycarbonate
Catalog Number	6110PCL3
EU RoHS Indicator	Yes
Item Type	NEXTSPEED 6-110 Connecting Block System
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	110 Punch Down
Series	Cat 6
Specifications	Material - Polycarbonate UL 94V-0
Temperature Rating	Per TIA

UPC 662620835877

Dimensions

Outside Diameter 0.218

Electrical Ratings

Voltage Rating 600V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#26-22 AWG

Certifications And Compliance

Industry Standard(s)	Exceeds TIA/EIA-568-C.2-1 Category 6 ConNECTing Hardware Specifications
----------------------	---

Logistics

Carton Quantity 20

Product Assets

[Specifications - 6110PCL3](#)
[Specifications - 6110PCL3 Specification Sheet English](#)