

HUBBELL Premise Wiring

6110PCL5

By Hubbell Premise Wiring
Catalog # [6110PCL5](#)



Patch Cord, 6-110 Factory Terminated Patch Cords, Cat6 (6-110 to 6-110), 5' Length

Features

- Plug Housing Includes Built-In Polarization to Ensure Proper Mating Connection to Connecting Blocks
- Angled Conductor Towers Separate Paired Conductors and makes Pair Splitting and Conductor Lacing Simple
- Cable Ties Secure Cable to Cover for Easy Termination and Strain Relief

Performance

Electrical - Terminates 24 to 26 AWG solid or 7-strand twisted-pair cable -

General

Attenuation	.1dB
Boot Type	Polycarbonate
Catalog Number	6110PCL5
EU RoHS Indicator	Yes
Item Type	NEXTSPEED 6-110 Connecting Block System
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	110 Punch Down
Series	Cat 6
Specifications	Material - Polycarbonate UL 94V-0
Temperature Rating	Per TIA

UPC 662620835884

Dimensions

Outside Diameter 0.218

Electrical Ratings

Voltage Rating 600V AC kV

Conductor Related

Conductor Stranding Stranded
Conductor Type Copper
Number of Conductors 8-Conductor
Wire Size #26-22 AWG

Certifications And Compliance

Industry Standard(s) Exceeds TIA/EIA-568-C.2-1
Category 6 ConNEcting
Hardware Specifications

Logistics

Carton Quantity 20

Product Assets

[Specifications - 6110PCL5 Specification Sheet English](#)
[Specifications - 6110PCL5](#)