

11-Gang CFB Series Box for
Rectangular Cover, 4.08" Minumum
Depth of Pour

By Hubbell Premise Wiring
Catalog # [CFB11G4](#)



Galvanized Stamped Steel Floor Box, Recessed, 11-Gang CFB
Series Box for Rectangular Cover, 4.08" Minumum Depth of Pour

Features

- Recessed 11-Gang Round Cover Floorbox
- For Use In Concrete Floors
- 4.08" Minimum Depth of Pour
- Box Includes Installation Cover
- Accepts industry Standard Size Wallplates

Application

- For Use in Concrete Floors

General

Application - For Use On	Concrete
Catalog Number	CFB11G4
Color	Metallic
Construction	Fabricated
EU RoHS Indicator	No
Knockouts	(4)3/4"-1", 9)1"- 1 1/2", 1) 1"-1 1/4", 4) 1"-1 1/4", 1)2"
Material	Pre Galvanized Steel
Mounting Method	Cast Into Concrete
Number of Gang(s)	11-Gang
Series	Recessed Rectangular - CFB Series
Size	11-Gang

Specifications

Type	Min. Depth of Pour - 4.08" (103.5)
UPC	11-Gang Recessed Floor Box 783585212937

Dimensions

Dimensions	13.5 in x 12.16 in x 4.08 in
Height	4.08 in
Length	13.5 in
Width	12.16 in

Conductor Related

Cable Entry	Through Cover
-------------	---------------

Certifications And Compliance

Industry Standard(s)	• UL/CSA • UL514
----------------------	--

Product Assets

[Brochures - Floorbox Selection Guide](#)
[Catalog Page - PREM T18 Catalog Page](#)
[Catalog Page - WDK O-37 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Premise Wiring Catalog](#)
[Specifications - CFB11G4](#)