

11-Gang CFB Series Box for Rectangular
Cover, 6.08" Minumum Depth of Pour

By Hubbell Premise Wiring
Catalog # [CFB11G6](#)

11-Gang CFB Box for Rectangular Cover, 6.08" Minumum Depth
of Pour



Features

- Recessed 11-Gang Round Cover Floorbox
- For Use In Concrete Floors
- 4.08" Minimum Depth of Pour
- Box Includes Installation Cover
- Accepts industry Standard Size Wallplates

Application

For Use in Concrete Floors

Specifications

Industry Standard(s)	• UL/CSA • UL514
EU RoHS Indicator	No

Conductor

Cable Entry	Through Cover
-------------	---------------

Configuration

Knockouts	(4)3/4"-1", 13)1"- 1 1/2", 1) 1"-1 1/4", 1)2"
Mounting Method	Cast Into Concrete
Number of Gang(s)	11-Gang

Dimensions

Size	11-Gang
Width	12.16 in
Height	6.08 in
Length	13.5 in
Dimensions	13.5 in x 12.16 in x 6.08 in

General

Construction	Fabricated
Type	11-Gang Recessed Floor Box
Series	Recessed Rectangular - CFB Series
Material	Pre Galvanized Steel
Specifications	Min. Depth of Pour - 6.08" (154.3)
UPC	783585212944
Application - For Use On	Concrete
Color	Metallic

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)