

Floor Boxes

SystemOne ETERNAL™ Series Concrete Floorboxes

4/5-Gang Recessed

HUBBELL

Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- External High Capacity Feed-Thru Hubs Sold Separately
- Stamped steel construction, exterior coated with fusion bonded epoxy paint for on grade use, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

Ordering Information

Cover Style	Box Type	Catalog Number	UPC Number
Round	On/ Above Grade	CFB45G55RCRE	783585695426

Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	16 gauge galvanized steel
Box Finish	Gray corrosion resistant epoxy paint
Top Mouning Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(2) Small 35 IN³ [574 CM³], (2) Med 69.5 IN³ [1139 CM³], (2) Large 99 IN³ [1622 CM³]

Performance

Height

6.31" [160.2mm]

Length

14.14" [359.2mm]

Trade Size Knock-Outs: Ends

(2) ¾", 1", 1¼", 2" (Field installed CFBHUB2 for 2" metallic conduit, CFBHUB200PVC for 2" PVC conduit or CFBHUB125PVC for 1¼" PVC condit)

Width

11.09" [281.6mm]



Accessories

(2) 2"PVC field installed hubs, ships with (2) 1-1/2" reducer, (2) 1-1/4" reducers, and (2) 1" reducers/plugs	CFBHUB200PVC
(2) 1-1/4" PVC field installed hubs, ships with (2) 1" reducers, (2) 3/4" reducers, AND (2) 1/2" reducer/plugs	CFBHUB125PVC
2" threaded zinc hub	CFBHUB2
3/4" Prepour stackable ring extensions	CFB8RCVRR075
(1) SyleLine Decorater Opening	FB10MPREC

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions