

Patch Cord, Fiber Optic, LC to LC,
Duplex Multi Mode, 50/125, 10GbE,
2 Meter Length



By Hubbell Premise Wiring
Catalog # [DFHPCLCLCE2MM](#)

Patch Cord, Fiber Optic, LC to LC, Duplex Multi Mode, 50/125, 10GbE, 2 Meter Length

Features

- Bend insensitive fiber

Application

Fiber Data Cross Connect

General

Catalog Number	DFHPCLCLCE2MM
Color	Aqua
Connector Type	LC-LC
Construction Material - Main	Plenum PVC
Sub Brand	FIBERHUBB
UPC	662620360911

Dimensions

Length (Meters)	2 m
-----------------	-----

Conductor Related

Fiber Type	OM3
Mode	multimode

Certifications And Compliance

Industry Standard(s)	• EIA/TIA-455/-604 • TIA-568-C.3
----------------------	--

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - PREM H3 CatalogPage](#)
- [Catalog Page - PREM H03 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Fiber Patch Cords Flyer](#)
- [Sales Drawings - HPW_DFPCLCLCE_DRAWING_PDF](#)
- [Specifications - DFHPCLCLCE2MM](#)