


Fiber Optic Patch Cord, Riser Rated,
MultiMode Duplex, LC-LC, OM4, 50 Meter

By Hubbell Premise Wiring
Catalog # [DFHRCLCLCF50MM](#)

FIBER, P-CORD,R,OM4,DUP,LC-LC,50M



Features

- Bend insensitive fiber

Application

Fiber Data Cross Connect

Specifications

- Industry Standard(s)
- EIA/TIA-455/-604
 - TIA-568-C.3

Conductor

Mode

multimode

Fiber Type

OM4

Dimensions

Length (Meters)

1 m

General

Color

Aqua

UPC

662620362373

Sub Brand

FIBERHUBB

Logistics

Carton Quantity

25