

HUBBELL  
Premise Wiring

Fiber Optic Patch Cord, Riser Rated,  
Singlemode Duplex, LC-LC, OS2, 5 Meter



By Hubbell Premise Wiring  
Catalog # [DFHRCLCLCS05SM](#)

FIBER, P-CORD,R,SM,DUP,LC-LC,0.5M

Features

- Bend insensitive fiber

Application

Fiber Data Cross Connect

Specifications

- |                      |                                                                                          |
|----------------------|------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• EIA/TIA-455/-604</li><li>• TIA-568-C.3</li></ul> |
|----------------------|------------------------------------------------------------------------------------------|

Conductor

|      |           |
|------|-----------|
| Mode | multimode |
|------|-----------|

|            |     |
|------------|-----|
| Fiber Type | OM4 |
|------------|-----|

Dimensions

|                 |     |
|-----------------|-----|
| Length (Meters) | 1 m |
|-----------------|-----|

General

|           |              |
|-----------|--------------|
| Color     | Aqua         |
| UPC       | 662620362380 |
| Sub Brand | FIBERHUBB    |

Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 25 |
|-----------------|----|