

Fiber Optic, Patch Cord, Plenum
Rated, OM4 Fiber, Duplex, LC-LC, 2
Meter Length



By Hubbell Premise Wiring
Catalog # [DFPCLCLCF2MM](#)

Fiber Optic, Patch Cord, Plenum Rated, OM4 Fiber, Duplex, LC-LC, 2 Meter Length.

Application

LC-LC

General

Catalog Number	DFPCLCLCF2MM
Color	Aqua
Connector Type	LC to LC
Construction Material - Main	Glass Fiber
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Patch Cords
Material	Glass Fiber
Size	OM4
Sub Brand	Fiber Optic Products
Temperature Rating	0 Degrees C to 75 Degree C
Type	OptiChannel Fiber Patch Cords
UPC	662620312705

Dimensions

Display Size	OM4
--------------	-----

Length (Meters)	2 m
Pitch	12

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Fiber Type	Plenum
Mode	OM4, MM
Wire Type	Multimode

Certifications And Compliance

Industry Standard(s)	TIA-568-C.3
----------------------	-------------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Specifications - DFPCLCLCF2MM Specification Sheet French](#)
[Specifications - DFPCLCLCF2MM Specification Sheet](#)