

Patch Cord, Fiber Optic, ST-Style to
ST-Style, Duplex Multi Mode,
62.5/125, 10 Meter Length, Orange



By Hubbell Premise Wiring
Catalog # [DFPCSTSTC10MM](#)

Patch Cord, Fiber Optic, ST-Style to ST-Style, Duplex Multi Mode,
62.5/125, 10 Meter Length, Orange

Application

ST to ST

General

Catalog Number	DFPCSTSTC10MM
Construction Material - Main	Glass Fiber
Insulation	PVC
Size	62.5 Micron, OM1
Sub Brand	Fiber Optic Products
Temperature Rating	0 Degrees C to 75 Degree C
Type	OptiChannel Fiber Patch Cords
UPC	662620802220

Dimensions

Length	32.8 ft
--------	---------

Length (Meters)	10 m
-----------------	------

Conductor Related

Fiber Type	OM1
Wire Type	Multimode

Certifications And Compliance

Industry Standard(s)	EIA/TIA-455/-604
----------------------	------------------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Specifications - DFPCSTSTC10MM](#)
- [Specifications - DFPCSTSTC10MM Specification Sheet English](#)