

OptiChannel

Fiber Connector

Singlemode

HUBBELL

Features

- Rugged Crimp Strain Relief
- Compatible with Heat Cure Epoxy
- 900 micron and 3.0mm Cable Applications

Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Connector, OPTIchannel Connector, LC Simplex Singlemode, 6 Pack	White	FCLCSM	662620830766



Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Performance

Environmental	
Operating temperature	0 °C to 70 °C
Mechanical	
Mating durability	500 cycles, 0.75dB
Optical	
Insertion loss	0.5dB typical, 0.75dB max
Multimode return loss	20dB minimum
Singlemode return loss	26dB minimum

Online Resources

eCatalog