

FiberHubb

FCR-X Rack Mount Enclosures

Enhanced 3U Enclosure with 12 LGX Slots,
Unloaded



Features

- Full 17" Depth, with Slide-Out/Tilt-Down Lower Tray
- Two-Piece Removable Top Covers
- Accepts all Standard FSP-Series Panels and OC-Series Cassettes
- Port assignment label clipped to front door
- Optional lock provisions on front and rear doors



Ordering Information

Description	Color	Catalog Number	UPC
Enhanced Rack Mount Enclosure	Black	FCR3U12SPX	662620368238

Listings

EIA/ECA-310-G
TIA-569-D

Specifications

Material	16 gauge, Cold-Rolled Steel
Rack Units	3
FSP Panel Capacity	12
Splice Tray Capacity	12
Max LC Port Capacity	288
Dimensions - In. (mm) (H x W x D)	5.25 (133) x 19 (483) x 17 (432)

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

