

FiberHubb

FCR-X Rack Mount Enclosures

Enhanced 4U Enclosure with 12 LGX Slots,
Vertical, Unloaded



- Features
- Full 17" Depth, with Slide-Out/Tilt-Down Lower Tray
 - Two-Piece Removable Top Covers
 - Accepts all Standard FSP-Series Panels and OC-Series Cassettes
 - Port assignment label clipped to front door
 - Optional lock provisions on front and rear doors



Ordering Information

Description	Color	Catalog Number	UPC
Enhanced Rack Mount Enclosure	Black	FCR4U12SPVX	662620368948

Listings

EIA/ECA-310-G
TIA-569-D

Specifications

Material	16 gauge, Cold-Rolled Steel
Rack Units	4
FSP Panel Capacity	12
Splice Tray Capacity	12
Max LC Port Capacity	288
Dimensions - In. (mm) (H x W x D)	7.0 (178) x 19 (483) x 17 (432)

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

