

FiberHUBB™

Rack Mount Enclosure

MPO UltraMax LC Duplex Frame

HUBBELL

- Features
- Straight and Angled Panel Versions
 - Easy-Slide Labeling System with Template
 - Detachable Cable Management Bar
 - MPO Male Input with up to 144 LC Output Ports
 - Custom Adapter Colors and Port Counts Available



Ordering Information

Description	Total LC	Catalog Number	UPC
MPO UltraMax, Straight Front, OS2, 144 Ports, Blue	144	FHD1U144LC12MPS	662620367675

Listings

EIA/ECA-310-E
TIA.569-D
RoHS Compliant

Specifications

Adapter Color	Blue
Connectivity	MPO to LC Duplex
Material - Enclosure	Cold-Rolled Steel
Dimensions	1.73 (44) x 17.65 (448) x 8.48 (215)
Fiber Type	OS2
LC Duplex Adapters	72
Total LC Ports	144
MPO Connector Type	Male, 12-Port
Total MPO Connectors	12
Polarity Type	A

Accessories

Rear Fiber Management Bar	HPRCMB
---------------------------	--------

Online Resources

eCatalog