

HUBBELL
Premise Wiring

Fiber, Pigtail, Bundle, 250 Micron, Buffered
Loose Tube, LC-Multi Mode, 6-Fiber
Strands, OM4 Fiber, 3 Meter

By Hubbell Premise Wiring
Catalog # [FHPBKLTR6LC4M](#)

Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, LC-Multi
Mode, 6-Fiber Strands, OM4 Fiber, 3 Meter

Features

- Bundle
- 250 Micron
- Buffered Loose Tube
- LC-Multi Mode
- 6-Fiber Strands

Application

Optical Signal

Conductor

Number Of Fibers	6
Conductor Type	Glass
Mode	OM4
Fiber Type	Riser
Wire Type	Multimode
Wire Size	50 Micron

Current

Connectivity	Plug-In
--------------	---------

Dimensions

Length (Meters)	3 m
Pitch	6
Outside Diameter	0.2

General

UPC	662620363127
Plug Type	LC-MM, 6F, 250LT, OM4
Material	Glass Fiber
Material - Jacket	Flame Redardant PVC
Material - Insulation	Flame Redardant PVC

Logistics

Carton Quantity	50
-----------------	----

Operational

Temperature Rating	TIA 568-C.3
--------------------	-------------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)

