

Fiber, Pigtail, Bundle, FC-Multi Mode, 12-Fiber Strands, OM1 Fiber, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPBKR12FC1M](#)

Fiber, Pigtail, Bundle, FC-Multi Mode, 12-Fiber Strands, OM1 Fiber, 3 Meter Length

Features

- Bundle
- FC-Multi Mode
- 12-Fiber Strands
- OM1 Fiber
- 3 Meter Length

Application

FC-MM

Conductor

Number Of Fibers	12
Mode	OM1
Fiber Type	Riser
Wire Type	Multimode

Current

Connectivity	Plug-In
--------------	---------

Dimensions

Length (Meters)	3 m
Pitch	12

General

UPC	662620363196
Material	Glass Fiber

Logistics

Carton Quantity	50
-----------------	----

Operational

Temperature Rating	0 Degrees C to 75 Degree C
--------------------	----------------------------

